

雙口玻璃瓶



雙口玻璃瓶	CPWYCP005 口徑 350 高度 140 瓶口直徑 × 75 瓶口
瓶口 瓶口直徑	5 瓶口直徑 瓶口直徑 瓶口 瓶口直徑 瓶口直徑 瓶口 15
瓶口	500 瓶口直徑 瓶口 瓶口
瓶口直徑 瓶口直徑	1 瓶口直徑 瓶口 瓶口直徑 24 瓶口直徑 瓶口 瓶口直徑 瓶口 瓶口直徑 瓶口 瓶口
瓶口直徑 瓶口	45 瓶口直徑 瓶口直徑 瓶口 瓶口
瓶口直徑 瓶口	30% 瓶口直徑 瓶口直徑 瓶口 瓶口 瓶口 瓶口 %70 瓶口直徑 瓶口直徑
瓶口	瓶口直徑 瓶口 瓶口 瓶口直徑 瓶口 瓶口 瓶口直徑 瓶口 瓶口







□□□□□□ □□□□ □□



□□□□□□□□ □□□□ □□□□



Cupwind

Q1: 00000 00000000 0000000 00 00 Cupwind

A1: □□□□□□ □□□□ □□□□□ □□□□ 25 □□□□□ 10-7 □□□□.

Q2: 如何 在 一个 线程 中 使用 Cupwind?

1200 個 50 個 個個個個 個個個個 個個個個 個個個 個個個個個 個個個個個 個個個 個 :20 個個個 個個個.

Q3: 如何设计 一个 叫 Cupwind

A1: 00000000 00000000 00000000 00000 50-35 0000.

```

00 000000 00000 000000 00 00 :4Cupwind

```

A1: 30% □□ □□□□ □□□□ □□□□ %70 □□□□□□ B/L 100 □□% L/C □□□□□□ □□.

0000 000000 0000 00000000 00000000 0000 00 00 :5 Cupwind

000 0000 00 :5 FOB 000000 000000 000 0000000 0000000 000000 0000 00 0000 000000 0000 000000 00

00000000 000000 000000 0000000 000000 0000 0000 0000 00 :6

0000000 00 0000000 0000000 0000 000000 0000 000000 00 0000 0000 :6

00000000 000000 000000 0000 0000000 0000 000000 000000 00 0000000 00 000000 0000 0000000.

0000 0000 000 :7 Cupwind 00000000 00000000

00 0000000 00000000 00000 00000 0000000 000000 0000000 0000 0000000 0000 00 :7 Cupwind 0000000000 0000000 .000000000 00000000 0000 00000000 0000000 00 000000 00000 00000 0000000 00000 00000 00000 0000 0000 00000 0000 00 000000 00000 000000000 00000 0000 00000000 00 00000 00000.



