

Titolo: Fornitura di vasetti di candele Iridescentei 8oz



La nostra forza

[Produttore di barattoli di candele iridescenti da 8 once Cina](#)

10000 mq di proprietà di laboratorio di decorazione.

20 tipi di diverse macchine per decorare.

20 anni di esperienza nel settore della decorazione.

20 fabbrica di vetro cooperativa stabile, fabbrica di ceramica, fabbrica di confezioni regalo, fabbrica di coperchi in metallo, supporto di fabbrica di coperchi in legno.

Marchi famosi in tutto il mondo come Porsche, Armani, Zara ecc.

Iridescent [barattolo di candela](#) è davvero NUOVA TENDENZA sul mercato, qualunque sia negli Stati Uniti, in Europa o in Australia, non solo lo fa su un barattolo di candele, ma anche su un bicchiere d'acqua, un bicchiere di birra, una bottiglia di whisky, un bicchiere di vino o anche sui barattoli di candele in ceramica, come Starbucks lo usa su boccali di birra e bicchieri d'acqua.

CARATTERISTICHE DEL PRODOTTO



Il MOQ del barattolo di candela iridescente è di soli 1000 pezzi, adatto alle piccole imprese. È una specie di galvanica, ma molto più colorato. Forniamo barattoli di candele iridescenti da più di 20 anni. In primo luogo è stato fatto sul camino della lampada. Alla gente è piaciuto molto questo bellissimo effetto e ha considerato di realizzarlo nel barattolo di candela che è stata un'ottima idea. Ci sono poche fabbriche in Cina che possono realizzare questo barattolo di candela iridescente di qualità di lusso.

Accessori



Wick Trimmer Cutter



Zinc Alloy Lid



Wooden Lid



Neck



Stopper



Reed



Gift Box.



Gift Box

Abbiamo alcuni accessori tra cui scegliere, come coperchio in legno e bambù, coperchio in metallo, vassoio in legno, set di rifinitori ecc.

SHENZHEN JIERUIMA TRADING CO., LTD
NO.415 RUNLIAN BUILDING, SHENZHU ROAD,
HENGANG, 518115, SHENZHEN, CHINA

LAB LOCATION: SHENZHEN
LAB NUMBER: (8521)097-0435

ATTN: EMMA ZOU
CC: emma@cupwind.com

DATE IN: APR 07, 2021
MOD. LOG IN: /
DATE OUT: APR 13, 2021
REVISED DATE:
WORKING DAYS: 5
PAGE: 2 OF 4

PASS	FAIL	DATA	X
admio, nor			

micol TESTING FOR
CA & LEAD & CADMIUM ON NON-FOOD /
BEVERAGE GLASSWARE-EXTERIOR

Sample Description:		IRIDESCENT COATING CANDLE JAR	
Manufacturer:	CUPWIND COOPERATED FACILITY	P.O. No.:	/
Buyer:	IPSY	Style:	/
Country of Origin:	CHINA	Country of Destination:	USA
Color:	IRIDESCENT	SKU Number:	ITEM#: 8090
Brand name:	CUPWIND ®		
Regulatory Denon No.:	Yes: ☐ No: ☒	Charge Vendor:	Yes: ☒ No: ☐


EXECUTIVE SUMMARY:

Test contents		Result Rating		
CA 65 Lead & Cadmium on non-biodegradable glassware-exterior		Met/Pass		
Effectiveness of annealing	ASTM F217-70-20 Sec 5 (Met)	With a tungsten carbide scribe, scratch once across the inside knuckle of the article. Then scratch an "X" across the entire inside bottom surface of the article. The scribe marks should be made using a procedure to first remove the burr on the glass. Then scratch each side with water at the same room temperature as the glass. Wait 15 minutes, then empty the water and examine the glass for fractures. Should the glass be cracked, determine the number of fractures, visually, for each fracture.	M	Pass
Thermal shock	ASTM F217-70-20 Sec 5 (Met) ASTM C149	Modification: expanded scope to all other glass products in addition to copse containers. Shall not crack or be cracked. If cracked, shall show a crack slowly that is less than 1/32" (0.25"). - prepare a hot bath at 71 ± 1 °C (160 ± 2°F) - Immerse the sample completely in the hot water bath and allow to soak for 5 min ± 0.1. - transfer the sample to the cold bath, and immerse for at least 30 - remove the sample from the cold bath and examine the sample for any cracking. Note: - the hot water that collects within the container during the first immersion shall be drained in the container through the second immersion - the time of transfer from the hot bath to the cold bath shall be 15 ± 1 s Modification: sampling procedure not followed and expanded scope to all other glass products in addition to copse containers.		Pass

REMARK:

1. No enclosed protocol for test results in this report

IMBALLAGGIO



Ogni bicchiere è avvolto da un sacchetto di plastica, quindi 48 pezzi in una scatola di cartone con divisori per uova. I pallet di legno sono sempre consigliati durante il trasporto, il che è molto più sicuro. Avremo una rete di corda di cotone nella porta del contenitore per tenerlo al

sicuro.