

## - Bekalan Pemegang Lilin Mercury Krismas China-



kekuatan kita

[pengeluar pemegang lilin christmas china](#)

Bengkel menghias 10000 meter persegi.

20 jenis mesin menghias yang berbeza.

20 tahun pengalaman dalam bidang menghias.

20 kilang kaca stabil menyokong.

Pembuatan jenama terkenal di seluruh dunia seperti Armani, Zara dll.

## CIRI-CIRI PRODUK

Cupwind adalah [Pembekal pemegang lilin Krismas China](#) , pemegang lilin diperbuat daripada kaca kapur soda. Berat, tahan lama, sesuai untuk bekas lilin. Hiasan taufan merkuri sangat sesuai untuk Krismas dan Perkahwinan.



Pemegang lilin merkuri mewah boleh dibuat dalam warna yang berbeza seperti gambar. Anda boleh mengisi bau yang berbeza dalam kaca berdasarkan warna yang berbeza.

## Kesan proses



Cupwind menerima reka bentuk tersuai OEM/ODM. Kami boleh mencipta bentuk anda sendiri dengan/tanpa nama jenama. Hiasan yang tersedia untuk penyemburan, penyaduran elektrik, lukisan logam, pelekat, setem panas, skrin sutera, sandblast, pemindahan air dll.



Wick Trimmer Cutter



Zinc Alloy Lid



Wooden Lid



Neck



Stopper



Reed



Gift Box



Gift Box

Kami menawarkan set aksesoris lilin dalam warna hitam, perak, emas, emas mawar, gangsa dan lain-lain. Tudung kayu, bahan kayu boleh didapati dalam MDF, Pine, Buluh, Beech, Walnut, Paulownia, Akasia, Kayu Getah, Oak Merah, Oak Putih, abu Eropah, Maple dll. Penutup logam, bahan logam boleh didapati dalam Timah, Keluli Tahan Karat, Aloi Zink, Besi Tahan Karat dll.



### TEST REPORT



(8521)097-0435  
Page 3 of 4

SHENZHEN JIERUIMA TRADING CO., LTD  
NO.415 RUNLIAN BUILDING, SHENZHU ROAD,  
HENGANGANG, 518115, SHENZHEN, CHINA

LAB LOCATION: SHENZHEN  
LAB NUMBER: (8521)097-0435

#### EXECUTIVE SUMMARY:

Test content	Result/Rating
CA 65 Lead & Cadmium on non-food beverage glassware-exterior	Meet/Pass

Semua tempahan balang lilin kadul dan botol etiga. Biasanya kami menggunakan ujian Cali 65 (ASTM (Annealing and Thermal Shock), ujian Plumbum dan Kadmium.

ATTN: EMMA ZOU  
4th Floor, Jieruima  
DATE OF TEST: APR 07, 2021  
MOD. CODE: /  
DATE OUT: APR 13, 2021  
REVISED DATE: /  
WORKING DAYS: 3  
REMARK: /

OVERALL RATING	
PASS	_____
FAIL	_____
DATA	_____

#### TESTING FOR CA 65 LEAD & CADMIUM ON NON-FOOD/ BEVERAGE GLASSWARE-EXTERIOR

Sample Description:	IRIDESCENT COATING CANDLE JAR	P.O. No.:	/
Manufacturer:	CUPWIND COOPERATED FACILITY	Style:	/
Buyer:	IPSY	Country of Destination:	USA
Country of Origin:	CHINA	SKU Number:	ITEM#: 8090
Color:	IRIDESCENT	Brand name:	CUPWIND®
Re-test:	Yes: <input type="checkbox"/> No: <input checked="" type="checkbox"/>	Charge Vendor:	Yes: <input checked="" type="checkbox"/> No: <input type="checkbox"/>
Previous Report No.:	/		

Effectiveness of treatment	ASTM F2179-20 Sec. 4.4 (Mod)	With a tungsten carbide scribe, scratch once along the inside surface of the jar. Then scratch in "X" pattern the whole inside bottom surface of the article. All scratches are to be made using sufficient pressure to just penetrate the surface of the glass. Fill each article with water at 15-20°C in a room temperature (20°C) glass. Wait 15 minutes, then empty the water and examine each piece for fractures. Shall show no fractures. Report the number of fractures, if any, for each test.	M	PASS
Thermal shock	ASTM F2179-20 Sec. 4.2 (Mod) / ASTM C149	Shall not crack or break after tested per below - prepare a cold-water bath at 21 ± 1 °C (70 ± 2°F). - prepare a hot bath at 71 ± 1.1 °C (160 ± 2°F) - immerse the sample completely in the hot water bath and allow to soak for 5 min ± 10 s. - transfer the sample to the cold bath, and immerse for at least 30 s. - remove the sample from the cold bath and examine the sample for any cracking. Note: - the hot water that collects within the container during the first immersion shall be retained in the container through the second immersion - the time of transfer from the hot bath to the cold bath shall be 15 ± 1 s Modification: sampling procedure not followed and expanded scope to all other glass products in addition to candle containers.	M	PASS

#### REMARK:

- No enclosed protocol for test results in this report.



## Pertunjukan Kilang



Cipwing mempunyai 10000 meter persegi bengkel menghias 20 jenis mesin menghias yang berbeza, 20 tahun pengalaman dalam kawasan menghias. 20 kilang kaca stabil menyokong dengan pabaga.

## Proses pembungkusan dan palet

Karton beralun dengan pembahagi papan silang, selamat untuk penghantaran antarabangsa. Kotak hadiah tersuai, keperluan kotak lembut boleh diterima.

