


**- Pemegang lilin kaca setem panas mengeluarkan
China -**



The [balang lilin kaca](#) menyembur warna biru telus, menggunakan pelekat cap panas emas, dengan isi lilin 11oz, dipadankan dengan penutup kayu pain. Mewah, klasik dan elegan, sesuai untuk majlis perkahwinan, hiasan rumah dll.



Pelekat setem panas emas ini adalah REKA BENTUK DAGANG oleh Cupwind, [setem panas pemegang lilin kaca pembuatan China](#), serta kotak hadiah yang sepadan. Bekas lilin biru telus dengan kotak hadiah biru anti-calar sangat sesuai untuk hiasan rumah gaya minimalis.



Kesan proses

Cupwind®
10



Cupwind menerima reka bentuk tersuai OEM/ODM. Kami boleh mencipta bentuk anda sendiri dengan/tanpa nama jenama. Hiasan ini tersedia untuk penyemburan, penyaduran elektrik, lukisan logam, pelekat, setem panas, skrin sutera, sandblast, pemindahan air dll.



Wick Trimmer Cutter



Zinc Alloy Lid



Wooden Lid



Neck



Stopper



Reed



Gift Box.



Gift Box

Kami tawarkan set aksesori lilin dalam warna hitam, perak, emas, emas mawar, gangsa dan lain-lain. Tudung kayu, bahan kayu boleh didapati dalam MDF, Pine, Buluh, Beech, Walnut, Paulownia, Acacia, Kayu getah, Oak Merah, Oak Putih, abu Eropah , Maple dll. Tudung logam, bahan logam boleh didapati dalam Timah, Keluli Tahan Karat, Aloi Zink, Besi Tahan Karat dll.



TEST REPORT

(852)097-0435
Page 3 of 4

Semua pesanan balang lilin kaca diuji oleh pihak ketiga. Biasanya kami menggunakan ujian Callout, Thermal Shock, ASTM (Annealing and Thermal Shock), Lead and Cadmium dan

Kadmium.

SHENZHEN JIERUIMA TRADING CO., LTD.
NO.415 FULIYAN BUILDING, SHENZHU ROAD,
HENGANG, 518115, SHENZHEN, CHINALAB LOCATION:
SHENZHEN
LAB NUMBER:
(852)097-0435

EXECUTIVE SUMMARY:

DATE IN:
APR 07, 2021MOD. LOC. IN:
CHINAREVISED DATE:
APR 07, 2021WORKING DAYS:
5PAGE:
2 OF 4OVERALL RATING:

PASS	X
FAIL	
DATA	

TESTING FOR
CA 65 LEAD & CADMIUM ON NON-FOOD/
BEVERAGE GLASSWARE-EXTERIOR

Sample Description:	IRIDESCENT COATING CANDLE JAR
Manufacturer:	CUPWIND COOPERATED FACILITY
P.O. No.:	/
Buyer:	IPSY
Country of Origin:	CHINA
Color:	IRIDESCENT
Brand name:	CUPWIND®
Re-test:	Yes: <input checked="" type="checkbox"/> No: <input type="checkbox"/>
Charge Vendor:	Yes: <input type="checkbox"/> No: <input checked="" type="checkbox"/>
Previous Report No.:	/

Test content:
CA 65 Lead & Cadmium on Non-Food/Beverage Glassware-ExteriorResult/Rating:
M: PASS
F: FAIL
P: Pending

Effectiveness of annealing: ASTM F2179-20 Sec. 4.2 (Mod)

With a tungsten carbide scriber, scratch once around the inside knuckle of the article. Then drop a 250°C (482°F) molten lead ball from a height of 10 cm onto the scratch. Allow the ball to roll until it comes to rest. If the ball penetrates the surface of the glass, fill each article with water at the same room temperature as the glass and heat it in a microwave oven for 1 min. Turn off the microwave oven and leave the glass in the microwave for another minute. Repeat the procedure until no new fractures appear. Report the number of fractures, if any, for each test.

Modification: expanded scope to all other glass products in addition to candle containers.

Thermal shock: ASTM F2179-20 Sec. 4.2 (Mod)/ASTM C149

Shall not crack or break after tested per below:

- prepare a cold-water bath at 21±1.1°C (70±2°F)

- prepare a hot bath at 71±1.1°C (160±2°F)

- immerse the sample completely in the hot water bath and allow to soak for 5 min ± 10 s.

- transfer the sample to the cold bath, and immediately immerse the sample.

- remove the sample from the cold bath and examine the sample for any cracking.

Note: The hot water that collects within the container during the first immersion shall be retained in the container through the second immersion.

- the time of transfer from the hot bath to the cold bath shall be 1±0.5 s.

Modification: sample procedure not followed and expanded scope to all other glass products in addition to candle containers.

REMARK:

- No enclosed protocol for test results in this report.



Pertunjukan Kilang



Cupwin mempunyai 10000 meter persegi bengkel manufaktur, 20 jenis mesin menghias yang berbeza, 20 tahun pengalaman dalam kawasan menghias, 20 kriang kaca stabil menyeluruh dengan pelbagai kapal kaca.

Proses pembungkusan dan palet

Karton beralun dengan pembahagi papan silang, selamat untuk penghantaran antarabangsa. Kotak hadiah tersuai, keperluan kotak lembut boleh diterima.

